

= Ĭ

-

## DX1009-T

The DX modular housing arrangement offers a flexible and space conscious solution to integrate our innovative DXO Cartridge in to both new and existing systems. The Delta-Xero system can be configured up to 12 cartridges in parallel as a single unit in a compact and easily maintainable layout.

The unit can be supplied with a number of standard options to provide an effective fluid conditioning and monitoring package to suit the majority of systems. The flexibility of the unit allows tailoring to customer's specific requirements.






## DX1009-T


Drive Input	Electric or Pneumatic							
Connection Ports	3/8"BSP In & Out							
Flow Indicator	Visual							
Suggested System Volume	Up to 40500ltrs @ 32cSt							
Particulate Removal	From 0,1 µ							
Weight	70 kg							
Dimensions	H 1158 mm x D 300 mm x L 1100 mm							
Material	SS316							
DXO Cartridge QTY	9							
Flow Rate varies depending on viscosity, pressure and temperature	Approx flow at 2.7 bar: Oil Volume	<b>32 cSt</b> 7.8 l/min 40500ltrs	<b>46 cSt</b> 6.75 l/min 31500ltrs	68 cSt 5.65 l/min 27000ltrs	<b>100 cSt</b> 4.65 l/min 21600ltrs	<b>220 cSt</b> 3.5 l/min 16200ltrs	<b>320 cSt</b> 1.75 l/min 7200ltrs	<b>460 cSt</b> 1.25 l/min 3600ltrs


© 2022 Delta-Xero All Rights Reserved. All information contained in this publication is indicative only and may be subject to change without prior notice

1

DELTA-XERO THE FUTURE IS SYSTEM RELIABILITY DX1009-T







## **DXO Cartridge**



Up to 4.5kg per DXO 2600ml

PP Cellulose mix

